


# TILTA CAMERA RIG FOR

## FOR SONY


A6300/A6400



CAGE HANDLES SUPPORT SYSTEM ACCESSORIES


1

Install the A6300/6400 camera into the cage



Mount the camera in the correct position and then insert and tighten the mounting screw


2



A limit stop is located on the cold shoe mount in the front of the top handle

15mm rod adapter can be used to mount EVFs or other accessories

3



Slide the top handle into the cold shoe mount and then fasten the knob (Optional)

Top handle is compatible with all Tiltaing cages

4

Note: Please select the correct quick release plate for your camera. Only one quick release plate is included in the package.

Quick release plate (Included)

Arca standard plate (Optional)

Manfrotto standard plate (Optional)

Rod adapter (Included)

Allows you to mount a Nucleus Nano motor or other accessories that mount onto a single 15mm rod

5

Single rod adapter (Optional)

Lens support (Optional)

HDMI and handle R/S cable mount (Included)

6

Slide the camera onto the baseplate until the stopper is bounced back, then fasten the lever (Optional)

For 15mm LWS rods

Tilta standard dovetail spacing

7

Side handle (Optional)

1/4"-20 to ARRI rosette attachment The function is shown below

Note: The correct attachment needs to be fastened depending on which side of the cage the handle will be attached.

1/4"-20 to ARRI rosette attachment (Optional)

This Universal converter is compatible with handles that have ARRI rosettes. This allows the handles to be mounted on the left or right side of the cage.